



use




For truss use only.
 Admrial Castor Ø 100 mm = WLL 160 kg
 Admrial Castor Ø 125 mm = WLL 200 kg




tips




secure with sufficient lashing straps




Easy storage:



max 2 m



max 2 m




keep on a flat surface

**ASSEMBLY KIT
STRONG BOY**


ZEM2SV34




2m or less use one cart



2m or less
use one cart



2m or more
use two carts



mount
Castor Ø 160 mm

maintenance

Please do not use aggressive cleaning agents such as solvents and/or corrosive substances. Clean the product and a cloth with a soft detergent. After cleaning the product dry it with a soft cloth. Check the product for wear and tear and/or lost items. By wear and/or missing of the proper components this product should be taken out of service immediately. Consult your supplier for advise.